



Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 10kVA

By Acme Electric
Catalog # [GP1210000S](#)



Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 10kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	GP1210000S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	277/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208/277 V
UL Insulation Class	180°C
UPC	047503001073
Winding Material	AL
kVA	10

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	125 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	6

Product Assets

- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - GP1210000S](#)
- [SDS - HCC SDS](#)
- [Specifications - GP1210000S](#)
- [Terms and Conditions - HCC Terms & Conditions](#)