



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 1kVA

By Acme Electric
Catalog # [T1001K0270CSH](#)

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 277/480 - 208/277V, 1kVA



*Representative Image

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	208/277 V
UL Insulation Class	180°C
Winding Material	CU
kVA	1

Dimensions

Dimensions	5.13 in x 5.5 in x 10.5 in
Height	10.5 in
Length	5.13 in
Weight	30 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	277/480 V

Certifications and Compliance

Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Installation Manuals - Acme Electric Manual A](#)
[SDS - HCC_SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME-T1001K0270CSH-SPEC-EN | REV 7/2023