



**Class 1, Div 2, Low Voltage
Distribution Transformer - Single
Phase, 120/208/240/277 -
120/240V, 7.5kVA**

By Acme Electric
Catalog # [T1007K0220CSH](#)



Class 1, Div 2, Low Voltage Distribution Transformer - Single
Phase, 120/208/240/277 - 120/240V, 7.5kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T1007K0220CSH
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
UL Insulation Class	180°C
Winding Material	AL
kVA	7.5

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in

Length	10.84 in
Weight	105 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)
[SDS - HCC SDS](#)
[Specifications - T1007K0220CSH](#)
[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)