



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 10kVA

By Acme Electric
Catalog # [T1010K0220CSH](#)



*Representative Image

Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 10kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
UL Insulation Class	180°C
Winding Material	AL
kVA	10

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	124 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

Certifications and Compliance

Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)

[Installation Manuals - Acme Electric Manual A](#)

[SDS - HCC_SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME-T1010K0220CSH-SPEC-EN | REV 7/2023