



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 25kVA

By Acme Electric
Catalog # T1025K0201CSH



Class 1, Div 2, Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 25kVA

Features

- Class 1 Div. 2, Groups A, B, C, D
- For Hazardous Locations
- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
Winding Material	AL
kVA	25

Dimensions

Dimensions	13.34 in x 16.13 in x 18.44 in
Height	18.44 in
Length	13.34 in
Weight	250 lb
Width	16.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications And Compliance

Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Brochures - Encapsulated Transformers for Hazardous Locations Class I, Div. 2](#)

[SDS - HCC SDS](#)

[Video - Encapsulated Transformers for Hazardous Locations Class I Div 2](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-T1025K0201CSH-SPEC-EN | REV 6/2024