



# Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 7.5kVA, 316 Stainless Steel

By Acme Electric  
Catalog # T253515SS



\*Representative Image

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 7.5kVA, 316 Stainless Steel

## Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503130582
Winding Material	AL
kVA	7.5

## Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	115 lb
Width	13.5 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [3D Models - Group\\_24](#)
- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Brochures - International Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Installation Manuals - Manual A-701953-A](#)
- [SDS - HCC\\_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-T253515SS-SPEC-EN | REV 1/2024