



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kVA

By Acme Electric
Catalog # T2535163S

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 10kVA



*Representative Image

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503734100
Winding Material	AL
kVA	10

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	125 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[3D Models - Group_24](#)
[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Brochures - International Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Customer Use Drawings - a-102722-b](#)
[Customer Use Drawings - a-125853](#)
[Customer Use Drawings - a-125877](#)
[Customer Use Drawings - a-125893](#)
[Customer Use Drawings - a-125885](#)
[Customer Use Drawings - a-700322](#)
[Customer Use Drawings - a-125883](#)
[Customer Use Drawings - a-125873](#)
[Customer Use Drawings - a-125881](#)
[Engineering Drawing - T2535163S](#)
[Installation Manuals - Acme Electric Manual A](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME-T2535163S-SPEC-EN | REV 7/2023