



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kVA, 316 Stainless Steel

By Acme Electric
Catalog # [T253518SS](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 25kVA, 316 Stainless Steel

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T253518SS
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503130612
Winding Material	AL
kVA	25

Dimensions

Dimensions	13.34 in x 16.13 in x 18.44 in
------------	--------------------------------

Height	18.44 in
Length	13.34 in
Weight	250 lb
Width	16.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - T253518SS](#)
[SDS - HCC SDS](#)
[Specifications - T253518SS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand