



# Low Voltage Distribution Transformer - Three Phase, 600? - 208Y/120V, 150kVA, Shielded

By Acme Electric  
Catalog # [T3150K0083BS](#)



Low Voltage Distribution Transformer - Three Phase, 600? - 208Y/120V, 150kVA, Shielded

### Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

### General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3150K0083BS
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	220°C
UPC	047503093450
Winding Material	AL
kVA	150

### Dimensions

Dimensions	29.87 in x 32.9 in x 41.52 in
Height	41.52 in

Length	29.87 in
Weight	970 lb
Width	32.9 in

### Electrical Ratings

Efficiency	98.83%
Frequency Rating	60 Hz
Primary Voltage	600D V

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

### Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)  
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Engineering Drawing - T3150K0083BS](#)  
[SDS - HCC SDS](#)  
[Specifications - T3150K0083BS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)