



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 100kVA, Non Ventillated

By Acme Electric
Catalog # [TE1530223S](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 100kVA, Non Ventillated

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	2
Catalog Number	TE1530223S
Construction	Non Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503090794
Winding Material	AL
kVA	100

Dimensions

Dimensions	30 in x 40 in x 42 in
Height	42 in
Length	30 in
Weight	775 lb
Width	40 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
ACME-TE1530223S-SPEC-EN | REV 6/2024