



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 50kVA

By Acme Electric
Catalog # [TP530203S](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 50kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA1

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503201510
Winding Material	AL
kVA	50

Dimensions

Dimensions	19.37 in x 24.39 in x 25.5 in
Height	25.5 in
Length	19.37 in
Weight	350 lb
Width	24.39 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 506

Product Assets

[3D Models - Group_40](#)
[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - TP530203S](#)
[Installation Manuals - Acme Electric Manual A](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)

Related Products

[WSA1 - Transformer Accessories, Weathershield Kit](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME-TP530203S-SPEC-EN | REV 7/2023