



## Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 75kVA

By Acme Electric  
Catalog # [TP531213S](#)

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 75kVA



\*Representative Image

### Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA3

### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503090169
Winding Material	AL
kVA	75

### Dimensions

Dimensions	26.88 in x 31.9 in x 35.47 in
Height	35.47 in
Length	26.88 in
Weight	430 lb
Width	31.9 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 2
UL Standard	UL 506

### Product Assets

[3D Models - Group\\_42](#)  
[Brochures - General Purpose Dry-Type Distribution Transformers](#)  
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)  
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)  
[Installation Manuals - Manual A-701953-A](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)

### Related Products

[WSA3 - Transformer Accessories, Weathershield Kit](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-TP531213S-SPEC-EN | REV 1/2024