



Low Voltage Distribution Transformer - Single Phase, 208 - 120/240V, 50kVA

By Acme Electric
Catalog # [TP536503S](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 208 - 120/240V, 50kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA1

General

| | |
|----------------------|-----------------------------------|
| Catalog Number | TP536503S |
| Construction | Ventilated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 150 Degrees Celsius |
| Mounting Type | Floor |
| Primary Voltage | 208 V |
| Product Category | Dry Type Distribution Transformer |
| Secondary Voltage | 120/240 V |
| UL Insulation Class | 220°C |
| UPC | 047503000090 |
| Winding Material | AL |
| kVA | 50 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 19.37 in x 24.39 in x 25.48 in |
| Height | 25.48 in |
| Length | 19.37 in |
| Weight | 340 lb |

Width 24.39 in

Electrical Ratings

| | |
|------------------|-------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 208 V |

Certifications And Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating | NEMA 2 |
| UL Standard | UL 506 |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
| Pallet Quantity | 1 |

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - TP536503S](#)
- [SDS - HCC SDS](#)
- [Specifications - TP536503S](#)
- [Terms and Conditions - HCC Terms & Conditions](#)