



## Medium Voltage Transformer - Single Phase, 4160 - 120/240V, 15kVA

By Acme Electric  
Catalog # [WB015K04](#)



\*Representative Image

Medium Voltage Transformer - Single Phase, 4160 - 120/240V,  
15kVA

### General

|                   |                            |
|-------------------|----------------------------|
| Construction      | Ventilated                 |
| Mounting Type     | Floor                      |
| Primary Voltage   | 4160                       |
| Product Category  | Medium Voltage Transformer |
| Secondary Voltage | 120/240 V                  |
| UPC               | 047503094785               |
| Winding Material  | AL                         |
| kVA               | 15                         |

### Dimensions

|        |         |
|--------|---------|
| Depth  | 17.0 in |
| Height | 32.0 in |
| Weight | 390 lb  |
| Width  | 26.5 in |

### Electrical Ratings

|                  |        |
|------------------|--------|
| Efficiency       | 98.10% |
| Frequency Rating | 60 Hz  |
| Primary Voltage  | 4160 V |

### Certifications and Compliance

|                           |  |
|---------------------------|--|
| CSA Standard              | C22.2 No. 47                             |
| Dept of Energy Regulation | Meets or exceed U.S. DOE 10 CFR Part 431 |
| Nema Rating               | NEMA 1                                   |
| UL Standard               | UL 1562                                  |

### Product Assets

[Brochures - MediumVoltageTransformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-WB015K04-SPEC-EN | REV 1/2024