



Medium Voltage Transformer - Single Phase, 4800 - 240/480V, 25kVA

By Acme Electric
Catalog # [WC025K08](#)



*Representative Image

Medium Voltage Transformer - Single Phase, 4800 - 240/480V,
25kVA

General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4800
Product Category	Medium Voltage Transformer
Secondary Voltage	240/480 V
UPC	047503096758
Winding Material	AL
kVA	25

Dimensions

Depth	20.0 in
Height	38.5 in
Weight	470 lb
Width	28.5 in

Electrical Ratings

Efficiency	98.12%
Frequency Rating	60 Hz
Primary Voltage	4800 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

[Brochures - MediumVoltageTransformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-WC025K08-SPEC-EN | REV 1/2024