



## Medium Voltage Transformer - Single Phase, 2400 - 120/240V, 333kVA

By Acme Electric  
Catalog # [WC333K01](#)

Medium Voltage Transformer - Single Phase, 2400 - 120/240V,  
333kVA



\*Representative Image

### General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400
Product Category	Medium Voltage Transformer
Secondary Voltage	120/240 V
UPC	047503097311
Winding Material	AL
kVA	333

### Dimensions

Depth	44.0 in
Height	80.0 in
Weight	2520 lb
Width	64.0 in

### Electrical Ratings

Efficiency	99.14%
Frequency Rating	60 Hz
Primary Voltage	2400 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - MediumVoltageTransformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-WC333K01-SPEC-EN | REV 1/2024