



Medium Voltage Transformer - Single Phase, 2400 - 600V, 333kVA

By Acme Electric
Catalog # [WC333K03](#)

Medium Voltage Transformer - Single Phase, 2400 - 600V,
333kVA



*Representative Image

General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400
Product Category	Medium Voltage Transformer
Secondary Voltage	600 V
UPC	047503097335
Winding Material	AL
kVA	333

Dimensions

Depth	44.0 in
Height	80.0 in
Weight	2520 lb
Width	64.0 in

Electrical Ratings

Efficiency	99.14%
Frequency Rating	60 Hz
Primary Voltage	2400 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

[Brochures - MediumVoltageTransformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.