



Medium Voltage Transformer - Three Phase, 2400Δ - 240ΔV, 15kVA

By Acme Electric
Catalog # [WH015K11](#)

Medium Voltage Transformer - Three Phase, 2400Δ - 240ΔV,
15kVA



*Representative Image

General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	240D V
UPC	047503097526
Winding Material	AL
kVA	15

Dimensions

Depth	17.0 in
Height	32.0 in
Weight	400 lb
Width	26.5 in

Electrical Ratings

Efficiency	97.50%
Frequency Rating	60 Hz
Primary Voltage	2400D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

[Brochures - MediumVoltageTransformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-WH015K11-SPEC-EN | REV 1/2024