



## Medium Voltage Transformer - Three Phase, 2400Δ - 480ΔV, 1500kVA

By Acme Electric  
Catalog # [WI015M12](#)

Medium Voltage Transformer - Three Phase, 2400Δ - 480ΔV,  
1500kVA



\*Representative Image

### General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	480D V
UPC	047503099506
Winding Material	AL
kVA	1500

### Dimensions

Depth	50.0 in
Height	90.0 in
Weight	7900 lb
Width	90.0 in

### Electrical Ratings

Efficiency	99.37%
Frequency Rating	60 Hz
Primary Voltage	2400D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - MediumVoltageTransformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-WI015M12-SPEC-EN | REV 1/2024