



## Medium Voltage Transformer - Three Phase, 2400Δ - 600Y//347V, 1500kVA

By Acme Electric  
Catalog # [WI015M15](#)



\*Representative Image

Medium Voltage Transformer - Three Phase, 2400Δ -  
600Y//347V, 1500kVA

### General

Catalog Number	WI015M15
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	600Y/347 V
UPC	047503099537
Winding Material	AL
kVA	1500

### Dimensions

Depth	50 in
Height	90 in
Weight	7900 lb
Width	90 in

### Electrical Ratings

Efficiency	99.37%
Frequency Rating	60 Hz
Primary Voltage	2400D V

### Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - Medium voltage dry-type transformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand