



## Medium Voltage Transformer - Three Phase, 4160 $\Delta$ - 480Y//277V, 30kVA

By Acme Electric  
Catalog # [WIO30K19](#)

Medium Voltage Transformer - Three Phase, 4160 $\Delta$  -  
480Y//277V, 30kVA



\*Representative Image

### General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4160 $\Delta$
Product Category	Medium Voltage Transformer
Secondary Voltage	480Y/277 V
UPC	047503097786
Winding Material	AL
kVA	30

### Dimensions

Depth	20.0 in
Height	38.5 in
Weight	485 lb
Width	28.5 in

### Electrical Ratings

Efficiency	97.90%
Frequency Rating	60 Hz
Primary Voltage	4160D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - MediumVoltageTransformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ACME-WIO30K19-SPEC-EN | REV 1/2024