



## Medium Voltage Transformer - Three Phase, 4800Δ - 480Y//277V, 45kVA

By Acme Electric  
Catalog # [W1045K25](#)

Medium Voltage Transformer - Three Phase, 4800Δ -  
480Y//277V, 45kVA



\*Representative Image

### General

Catalog Number	W1045K25
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4800Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	480Y/277 V
UPC	047503098011
Winding Material	AL
kVA	45

### Dimensions

Depth	21.8 in
Height	40.5 in
Weight	580 lb
Width	31.5 in

### Electrical Ratings

Efficiency	97.86%
Frequency Rating	60 Hz
Primary Voltage	4800D V

### Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - Medium voltage dry-type transformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand