



Medium Voltage Transformer - Three Phase, 2400Δ - 600ΔV, 112.5kVA

By Acme Electric
Catalog # [WI112K14](#)

Medium Voltage Transformer - Three Phase, 2400Δ - 600ΔV,
112.5kVA



*Representative Image

General

| | |
|-------------------|----------------------------|
| Construction | Ventilated |
| Mounting Type | Floor |
| Primary Voltage | 2400Δ |
| Product Category | Medium Voltage Transformer |
| Secondary Voltage | 600D V |
| UPC | 047503098264 |
| Winding Material | AL |
| kVA | 112.5 |

Dimensions

| | |
|--------|---------|
| Depth | 21.8 in |
| Height | 40.5 in |
| Weight | 940 lb |
| Width | 36.5 in |

Electrical Ratings

| | |
|------------------|---------|
| Efficiency | 98.52% |
| Frequency Rating | 60 Hz |
| Primary Voltage | 2400D V |

Certifications and Compliance

| | |
|---------------------------|------------------------------------------|
| CSA Standard | C22.2 No. 47 |
| Dept of Energy Regulation | Meets or exceed U.S. DOE 10 CFR Part 431 |
| Nema Rating | NEMA 1 |
| UL Standard | UL 1562 |

Product Assets

[Brochures - MediumVoltageTransformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ACME-WI112K14-SPEC-EN | REV 1/2024