



## Medium Voltage Transformer - Three Phase, 2400Δ - 240ΔV, 225kVA

By Acme Electric  
Catalog # WI225K11

Medium Voltage Transformer - Three Phase, 2400Δ - 240ΔV,  
225kVA



\*Representative Image

### General

Catalog Number	WI225K11
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	240D V
UPC	047503098592
Winding Material	AL
kVA	225

### Dimensions

Depth	26.5 in
Height	51.5 in
Weight	1480 lb
Width	40.5 in

### Electrical Ratings

Efficiency	98.82%
Frequency Rating	60 Hz
Primary Voltage	2400D V

### Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

[Brochures - Medium voltage dry-type transformers](#)  
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand