



Medium Voltage Transformer - Three Phase, 2400Δ - 240ΔV, 225kVA

By Acme Electric
Catalog # [WI225K11](#)



*Representative Image

Medium Voltage Transformer - Three Phase, 2400Δ - 240ΔV,
225kVA

General

Catalog Number	WI225K11
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	240D V
UPC	047503098592
Winding Material	AL
kVA	225

Dimensions

Depth	26.5 in
Height	51.5 in
Weight	1480 lb
Width	40.5 in

Electrical Ratings

Efficiency	98.82%
------------	--------

Frequency Rating	60 Hz
Primary Voltage	2400D V

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

- [Brochures - Medium voltage dry-type transformers](#)
- [Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
- [Customer Notices - Prop65_Cancer](#)
- [SDS - HCC SDS](#)
- [Specifications - WI225K11](#)
- [Terms and Conditions - HCC Terms & Conditions](#)