



Medium Voltage Transformer - Three Phase, 4800Δ - 600Y//347V, 225kVA

By Acme Electric
Catalog # [WI225K27](#)

Medium Voltage Transformer - Three Phase, 4800Δ -
600Y//347V, 225kVA



*Representative Image

General

Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4800Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	600Y/347 V
UPC	047503098752
Winding Material	AL
kVA	225

Dimensions

Depth	26.5 in
Height	51.5 in
Weight	1480 lb
Width	40.5 in

Electrical Ratings

Efficiency	98.69%
Frequency Rating	60 Hz
Primary Voltage	4800D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

[Brochures - MediumVoltageTransformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Installation Manuals - General Purpose Dry-Type Distribution Transformer](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.