



Medium Voltage Transformer - Three Phase, 2400? - 208Y/120V, 300kVA

By Acme Electric
Catalog # [WI300K10](#)



*Representative Image

Medium Voltage Transformer - Three Phase, 2400? - 208Y/120V,
300kVA

General

Catalog Number	WI300K10
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	208Y/120 V
UPC	047503098769
Winding Material	AL
kVA	300

Dimensions

Depth	32 in
Height	66 in
Weight	1980 lb
Width	50.5 in

Electrical Ratings

Efficiency	98.93%
Frequency Rating	60 Hz
Primary Voltage	2400D V

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

- [Brochures - Medium voltage dry-type transformers](#)
- [Customer Notices - Prop65_Cancer](#)
- [SDS - HCC SDS](#)
- [Specifications - WI300K10](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand