



# Medium Voltage Transformer - Three Phase, 4800? - 208Y//120V, 750kVA

By Acme Electric  
Catalog # [WI750K22](#)



\*Representative Image

Medium Voltage Transformer - Three Phase, 4800? -  
208Y//120V, 750kVA

### General

|                   |                            |
|-------------------|----------------------------|
| Catalog Number    | WI750K22                   |
| Construction      | Ventilated                 |
| Mounting Type     | Floor                      |
| Primary Voltage   | 4800Δ                      |
| Product Category  | Medium Voltage Transformer |
| Secondary Voltage | 208Y/120 V                 |
| UPC               | 047503099254               |
| Winding Material  | AL                         |
| kVA               | 750                        |

### Dimensions

|        |         |
|--------|---------|
| Depth  | 44 in   |
| Height | 80 in   |
| Weight | 4750 lb |
| Width  | 64 in   |

### Electrical Ratings

|                  |         |
|------------------|---------|
| Efficiency       | 99.12%  |
| Frequency Rating | 60 Hz   |
| Primary Voltage  | 4800D V |

### Certifications And Compliance

|                           |   |
|---------------------------|---|
| Buy America(n) Qualified  | Contact Manufacturer                        |
| CSA Standard              | C22.2 No. 47                                |
| Dept of Energy Regulation | Meets or exceed U.S. DOE 10<br>CFR Part 431 |
| Nema Rating               | NEMA 1                                      |
| UL Standard               | UL 1562                                     |

### Product Assets

- [Brochures - Medium voltage dry-type transformers](#)
- [Customer Notices - Prop65\\_Cancer](#)
- [SDS - HCC SDS](#)
- [Specifications - WI750K22](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand