



Medium Voltage Transformer - Three Phase, 4800Δ - 600Y//347V, 750kVA

By Acme Electric
Catalog # [WI750K27](#)

Medium Voltage Transformer - Three Phase, 4800Δ -
600Y//347V, 750kVA



*Representative Image

General

Catalog Number	WI750K27
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4800Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	600Y/347 V
UPC	047503099308
Winding Material	AL
kVA	750

Dimensions

Depth	44 in
Height	80 in
Weight	4750 lb
Width	64 in

Electrical Ratings

Efficiency	99.12%
Frequency Rating	60 Hz
Primary Voltage	4800D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Brochures - Medium voltage dry-type transformers](#)
[Catalogs - Acme Electric Catalog - Section 2 - Medium Voltage Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)

