



# Panel-Tran Zone Power Centers - Three Phase, 480? - 208Y/120V, 30kVA, Bolt In Breakers

By Acme Electric  
Catalog # [PTBB3150030LS](#)



Panel-Tran Zone Power Centers - Three Phase, 480? - 208Y/120V, 30kVA, Bolt In Breakers

### Features

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

### General

ANFC Taps	-
BNFC Taps	2
Catalog Number	PTBB3150030LS
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Breaker	ED43B090L (90A)
Primary Voltage	480
Product Category	Panel-Tran Zone Power Centers
Secondary Breaker	B3100 (100A)
Secondary Voltage	208Y/120 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503090367
Winding Material	AL
kVA	30

### Dimensions

Dimensions	13.75 in x 33 in x 43.75 in
------------	-----------------------------

Height	43.75 in
Length	13.75 in
Weight	680 lb
Width	33 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

### Certifications And Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 1062

### Logistics

Carton Quantity	1
Pallet Quantity	1

### Product Assets

- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - PTBB3150030LS](#)
- [Specifications - PTBB3150030LS Specification Sheet English](#)
- [Specifications - PTBB3150030LS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)