



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.05kVA

By Acme Electric
Catalog # [T153004](#)



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.05kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T153004
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	130°C
UPC	047503086285
Winding Material	CU
kVA	0.1

Dimensions

Dimensions	3.05 in x 3.14 in x 6.41 in
Height	6.41 in
Length	3.05 in
Weight	4 lb
Width	3.14 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	3
Pallet Quantity	250

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Use Drawings - a-125875](#)
[Customer Use Drawings - a-125855](#)
[Engineering Drawing - T153004](#)
[SDS - HCC SDS](#)
[Specifications - T153004](#)
[Specifications - T153004 Specification Sheet French](#)
[Specifications - T153004 Specification Sheet English](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand