



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.1kVA

By Acme Electric
Catalog # [T153005](#)



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.1kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T153005
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	130°C
UPC	047503085349
Winding Material	CU
kVA	0.1

Dimensions

Dimensions	3.67 in x 3.89 in x 7.16 in
Height	7.16 in
Length	3.67 in
Weight	5 lb
Width	3.89 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	3
Pallet Quantity	252

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Use Drawings - a-125875](#)
- [Customer Use Drawings - a-125855](#)
- [Engineering Drawing - T153005](#)
- [SDS - HCC SDS](#)
- [Specifications - T153005 Specification Sheet English](#)
- [Specifications - T153005 Specification Sheet French](#)
- [Specifications - T153005](#)
- [Terms and Conditions - HCC Terms & Conditions](#)