



Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 7.5kVA

By Acme Electric
Catalog # [T243570](#)

Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 7.5kVA

Features

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

General

Catalog Number	T243570
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Buck-Boost Transformer
Secondary Voltage	24/48 V
UL Insulation Class	180°C
UPC	047503182505
Winding Material	AL
kVA	7.5

Dimensions

Dimensions	10.84 in x 11.12 in x 20.81 in
Height	20.81 in
Length	10.84 in
Weight	135 lb
Width	11.12 in

Electrical Ratings



*Representative Image

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Brochures - Buck-Boost Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 7 - Buck Boost Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - T243570 Specification Sheet French](#)
- [Specifications - T243570 Specification Sheet English](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - Buck Boost Transformers](#)
- [Video - Product Information Video Series - Buck Boost Transformers](#)