



Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 10kVA

By Acme Electric
Catalog # [T243571](#)

Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 10kVA

Features

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

General

Catalog Number	T243571
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Buck-Boost Transformer
Secondary Voltage	24/48 V
UL Insulation Class	180°C
UPC	047503086292
Winding Material	AL
kVA	10

Dimensions

Dimensions	11.59 in x 11.75 in x 20.81 in
Height	20.81 in
Length	11.59 in
Weight	160 lb
Width	11.75 in

Electrical Ratings



*Representative Image

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Brochures - Buck-Boost Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 7 - Buck Boost Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - T243571 Specification Sheet French](#)
- [Specifications - T243571 Specification Sheet English](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - Buck Boost Transformers](#)
- [Video - Product Information Video Series - Buck Boost Transformers](#)