



Low Voltage Distribution Transformer - Three Phase, 600/480 - 480/380V, 45/36kVA, Autotransformer

By Acme Electric
Catalog # [T2527071](#)

Low Voltage Distribution Transformer - Three Phase, 600/480 - 480/380V, 45/36kVA, Autotransformer

Features

- Quiet operation with sound levels below NEMA standards

General

BNFC Taps	2
Catalog Number	T2527071
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480/380 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	004750342007
Winding Material	AL
kVA	45/36

Dimensions

Dimensions	7.37 in x 19.25 in x 15.21 in
Height	15.21 in
Length	7.37 in
Weight	156 lb
Width	19.25 in



*Representative Image

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600/480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	8

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - T2527071](#)
[SDS - HCC SDS](#)
[Specifications - T2527071 Specification Sheet French](#)
[Specifications - T2527071 Specification Sheet English](#)
[Specifications - T2527071](#)
[Terms and Conditions - HCC Terms & Conditions](#)