



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.75kVA, 316 Stainless Steel

By Acme Electric
Catalog # [T253009SS](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.75kVA, 316 Stainless Steel

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T253009SS
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	155°C
UPC	047503130520
Winding Material	CU
kVA	0.75

Dimensions

Dimensions	4.5 in x 4.75 in x 9.68 in
Height	9.68 in
Length	4.5 in
Weight	19 lb
Width	4.75 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	20

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - T253009SS](#)
[SDS - HCC SDS](#)
[Specifications - T253009SS](#)
[Specifications - T253009SS Specification Sheet French](#)
[Specifications - T253009SS Specification Sheet English](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand