



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 1.5kVA, 316 Stainless Steel

By Acme Electric
Catalog # T253011SS



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 1.5kVA, 316 Stainless Steel.

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T253011SS
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503087756
Winding Material	CU
kVA	1.5

Dimensions

Dimensions	5.13 in x 5.5 in x 11.62 in
Height	11.62 in
Length	5.13 in
Weight	30 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	72

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - T253011SS](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)