



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 2kVA

By Acme Electric
Catalog # [T253012S](#)



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 2kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T253012S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503084267
Winding Material	CU
kVA	2

Dimensions

Dimensions	5.13 in x 5.5 in x 13 in
Height	13 in
Length	5.13 in
Weight	38 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Primary Voltage	240 X 480 V
-----------------	-------------

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	20

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Customer Use Drawings - a-125875](#)
[Customer Use Drawings - a-32817-b](#)
[Customer Use Drawings - a-125849](#)
[Customer Use Drawings - a-35633](#)
[Customer Use Drawings - a-125855](#)
[Customer Use Drawings - a-700319](#)
[Engineering Drawing - T253012S](#)
[SDS - HCC SDS](#)
[Specifications - T253012S](#)
[Specifications - T253012S Specification Sheet English](#)
[Specifications - T253012S Specification Sheet French](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand