



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 3kVA

By Acme Electric
Catalog # [T2530134S](#)



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 3kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T2530134S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503001264
Winding Material	CU
kVA	3

Dimensions

Dimensions	7.13 in x 10.31 in x 11.5 in
Height	11.5 in
Length	7.13 in
Weight	55 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Primary Voltage	240 X 480 V
-----------------	-------------

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	24

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Customer Use Drawings - a-125850](#)
- [Customer Use Drawings - a-125876](#)
- [Customer Use Drawings - a-125872](#)
- [Customer Use Drawings - a-125884](#)
- [Customer Use Drawings - a-102723](#)
- [Engineering Drawing - T2530134S](#)
- [SDS - HCC SDS](#)
- [Specifications - T2530134S Specification Sheet English](#)
- [Specifications - T2530134S](#)
- [Specifications - T2530134S Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)