



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 5kVA

By Acme Electric
Catalog # [T2530144S](#)



Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 5kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T2530144S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503090558
Winding Material	CU
kVA	5

Dimensions

Dimensions	7.13 in x 10.31 in x 14.38 in
Height	14.38 in
Length	7.13 in
Weight	75 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Primary Voltage	240 X 480 V
-----------------	-------------

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	24

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Customer Use Drawings - a-125850](#)
[Customer Use Drawings - a-125876](#)
[Customer Use Drawings - a-125892](#)
[Customer Use Drawings - a-125851](#)
[Customer Use Drawings - a-125872](#)
[Customer Use Drawings - a-102723](#)
[Engineering Drawing - T2530144S](#)
[SDS - HCC SDS](#)
[Specifications - T2530144S Specification Sheet French](#)
[Specifications - T2530144S Specification Sheet English](#)
[Specifications - T2530144S](#)
[Terms and Conditions - HCC Terms & Conditions](#)