



Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 25kVA

By Acme Electric
Catalog # [T2536181S](#)



Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 25kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

BNFC Taps	2
Catalog Number	T2536181S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503734605
Winding Material	AL
kVA	25

Dimensions

Dimensions	13.34 in x 16.13 in x 18.44 in
Height	18.44 in
Length	13.34 in
Weight	250 lb
Width	16.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	4

Product Assets

- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Customer Use Drawings - a-125861](#)
- [Customer Use Drawings - a-125863](#)
- [Engineering Drawing - T2536181S](#)
- [SDS - HCC SDS](#)
- [Specifications - T2536181S Specification Sheet](#)
- [Specifications - T2536181S Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)