



**Low Voltage Distribution
Transformer - Single Phase,
120/208/240/277 - 120/240V,
7.5kVA**

By Acme Electric
Catalog # [T279745S](#)



Low Voltage Distribution Transformer - Single Phase,
120/208/240/277 - 120/240V, 7.5kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Catalog Number	T279745S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 / 208 / 240 / 277 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503102107
Winding Material	AL
kVA	7.5

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	105 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	6

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - T279745S](#)
[SDS - HCC SDS](#)
[Specifications - T279745S Spec Sheet](#)
[Specifications - T279745S Specification Sheet](#)
[Specifications - T279745S Specification Sheet French](#)
[Terms and Conditions - HCC Terms & Conditions](#)