



Low Voltage Distribution Transformer - Three Phase, 600? - 240?120V, 15kVA, Shielded

By Acme Electric
Catalog # [T3015K0323BS](#)



Low Voltage Distribution Transformer - Three Phase, 600? - 240?120V, 15kVA, Shielded

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

ANFC Taps	2
BNFC Taps	4
Catalog Number	T3015K0323BS
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	240D 120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503092767
Winding Material	AL/CU
kVA	15

Dimensions

Dimensions	19.37 in x 24.39 in x 25.5 in
Height	25.5 in
Length	19.37 in
Weight	290 lb
Width	24.39 in

Electrical Ratings

Efficiency	97.89%
Frequency Rating	60 Hz
Primary Voltage	600D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561

Logistics

Carton Quantity	1
Pallet Quantity	1

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop65_Cancer](#)
[Engineering Drawing - T3015K0323BS](#)
[SDS - HCC SDS](#)
[Specifications - T3015K0323BS Specification Sheet French](#)
[Specifications - T3015K0323BS](#)
[Specifications - T3015K0323BS Specification Sheet](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand