



**Low Voltage Distribution
Transformer - Single Phase,
190/200/208/220 X
380/400/416/440 - 120/240V,
3kVA**

By Acme Electric
Catalog # [TF249873S](#)



Low Voltage Distribution Transformer - Single Phase,
190/200/208/220 X 380/400/416/440 - 120/240V, 3kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

CE Compliant	CE Marked
Catalog Number	TF249873S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 200 / 208 / 220 X 380 / 400 / 416 / 440 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503087305
Winding Material	CU
kVA	3

Dimensions

Dimensions	7.13 in x 10.31 in x 11.5 in
Height	11.5 in
Length	7.13 in
Weight	55 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------

Primary Voltage	190/200/208/220 X 380/400/416/440 V
-----------------	--

Certifications And Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	24

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Customer Use Drawings - a-700601](#)
[Customer Use Drawings - a-700602](#)
[Customer Use Drawings - a-700592](#)
[Customer Use Drawings - a-700598](#)
[Customer Use Drawings - a-700599](#)
[Customer Use Drawings - a-700600](#)
[Engineering Drawing - TF249873S](#)
[SDS - HCC SDS](#)
[Specifications - TF249873S Specification Sheet French](#)
[Specifications - TF249873S](#)
[Specifications - TF249873S Specification Sheet English](#)
[Terms and Conditions - HCC Terms & Conditions](#)