



**Low Voltage Distribution
Transformer - Single Phase,
190/208/220/240 X
380/416/440/480 - 120/240V,
3kVA**

By Acme Electric
Catalog # [TF279262S](#)



Low Voltage Distribution Transformer - Single Phase,
190/208/220/240 X 380/416/440/480 - 120/240V, 3kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

CE Compliant	CE Marked
Catalog Number	TF279262S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 208 / 220 / 240 X 380 / 416 / 440 / 480 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503400043
Winding Material	CU
kVA	3

Dimensions

Dimensions	7.13 in x 10.31 in x 11.5 in
Height	11.5 in
Length	7.13 in
Weight	55 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/208/220/240 X 380/416/440/480 V

Certifications And Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	12

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - TF279262S](#)
[SDS - HCC SDS](#)
[Specifications - TF279262S](#)
[Specifications - TF279262S Specification Sheet French](#)
[Specifications - TF279262S Specification Sheet English](#)
[Terms and Conditions - HCC Terms & Conditions](#)