



Low Voltage Distribution Transformer - Single Phase, 190/208/220/240 X 380/416/440/480 - 120/240V, 25kVA

By Acme Electric
Catalog # [TF279267S](#)

Low Voltage Distribution Transformer - Single Phase,
190/208/220/240 X 380/416/440/480 - 120/240V, 25kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

CE Compliant	CE Marked
Catalog Number	TF279267S
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 208 / 220 / 240 X 380 / 416 / 440 / 480 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503420973
Winding Material	AL
kVA	25

Dimensions

Dimensions	13.34 in x 16.13 in x 18.44 in
Height	18.44 in
Length	13.34 in
Weight	300 lb
Width	16.13 in



Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/208/220/240 X 380/416/440/480 V

Certifications And Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Logistics

Carton Quantity	1
Pallet Quantity	6

Product Assets

[Brochures - General Purpose Dry-Type Distribution Transformers](#)
[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - TF279267S](#)
[SDS - HCC SDS](#)
[Specifications - TF279267S Spec Sheet](#)
[Specifications - TF279267S Specification Sheet French](#)
[Specifications - TF279267S Specification Sheet](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
ACME_CA-TF279267S-SPEC-EN | REV 4/2025