



# Medium Voltage Transformer - Single Phase, 2400 - 600V, 250kVA

By Acme Electric  
Catalog # [WC250K02](#)

Medium Voltage Transformer - Single Phase, 2400 - 600V,  
250kVA



\*Representative Image

### General

Catalog Number	WC250K02
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	2400
Product Category	Medium Voltage Transformer
Secondary Voltage	240/480 V
UPC	047503097243
Winding Material	AL
kVA	250

### Dimensions

Depth	32 in
Height	40.8 in
Weight	2030 lb
Width	50.5 in

### Electrical Ratings

Efficiency	99.07%
Frequency Rating	60 Hz
Primary Voltage	2400 V

### Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

### Product Assets

- [Brochures - Medium voltage dry-type transformers](#)
- [Customer Notices - Prop65\\_Cancer](#)
- [SDS - HCC SDS](#)
- [Specifications - WC250K02 Specification Sheet French](#)
- [Specifications - WC250K02 Specification Sheet English](#)
- [Terms and Conditions - HCC Terms & Conditions](#)