



Medium Voltage Transformer - Three Phase, 4800? - 600Y//347V, 225kVA

By Acme Electric
Catalog # [WI225K27](#)



*Representative Image

Medium Voltage Transformer - Three Phase, 4800? -
600Y//347V, 225kVA

General

Catalog Number	WI225K27
Construction	Ventilated
Mounting Type	Floor
Primary Voltage	4800Δ
Product Category	Medium Voltage Transformer
Secondary Voltage	600Y/347 V
UPC	047503098752
Winding Material	AL
kVA	225

Dimensions

Depth	26.5 in
Height	51.5 in
Weight	1480 lb
Width	40.5 in

Electrical Ratings

Efficiency	98.69%
Frequency Rating	60 Hz
Primary Voltage	4800D V

Certifications And Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 1
UL Standard	UL 1562

Product Assets

- [Brochures - Medium voltage dry-type transformers](#)
- [Customer Notices - Prop65_Cancer](#)
- [SDS - HCC SDS](#)
- [Specifications - WI225K27 Specification Sheet French](#)
- [Specifications - WI225K27 Specification Sheet English](#)
- [Terms and Conditions - HCC Terms & Conditions](#)