



Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 10kVA

By Acme Electric
Catalog # [T279746S](#)

Low Voltage Distribution Transformer - Single Phase,
120/208/240/277 - 120/240V, 10kVA



*Representative Image

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 / 208 / 240 / 277 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503102121
Winding Material	AL
kVA	10

Dimensions

Dimensions	10.84 in x 13.5 in x 15.19 in
Height	15.19 in
Length	10.84 in
Weight	124 lb
Width	13.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

[3D Models - Group_24](#)

[Brochures - General Purpose Dry-Type Distribution Transformers](#)

[Brochures - International Transformers](#)

[Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)

[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)

[Engineering Drawing - T279746S](#)

[Installation Manuals - Acme Electric Manual A](#)

[SDS - HCC_SDS](#)

[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME_T279746S_SPEC | REV 3/2023