



Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 15kVA

By Acme Electric
Catalog # [T279747S](#)



*Representative Image

Low Voltage Distribution Transformer - Single Phase, 120/208/240/277 - 120/240V, 15kVA

Features

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 / 208 / 240 / 277 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503102145
Winding Material	AL
kVA	15

Dimensions

Dimensions	11.59 in x 14.12 in x 16.94 in
Height	16.94 in
Length	11.59 in
Weight	171 lb
Width	14.12 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506

Product Assets

- [3D Models - Group_25](#)
- [Brochures - General Purpose Dry-Type Distribution Transformers](#)
- [Brochures - International Transformers](#)
- [Catalogs - Acme Electric Catalog - Section 1 - Dry-Type Distribution Transformers](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - T279747S](#)
- [Installation Manuals - Acme Electric Manual A](#)
- [SDS - HCC_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ACME_T279747S_SPEC | REV 3/2023